

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

©

COPYRIGHT

By

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FS1.27N, FS1.78N SERIES

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margin (G)	POS
1-1447169-5	FS1.27N18A11 JUMPER NOMEX	1.27	18.0	3.18	0.35MAX	0.84MAX	φ 0.32	0.25MIN	11
2-1447169-8	FS1.27N33A30 JUMPER NOMEX	1.27	33.0	3.18	0.35MAX	0.84MAX	φ 0.32	0.25MIN	30
7-1447169-8	FS1.78N25.4A30 JUMPER NOMEX	1.78	25.4	3.18	0.35MAX	0.84MAX	φ 0.40	0.25MIN	30
8-1447169-9	FS1.78N38.1A40 JUMPER NOMEX	1.78	38.1	3.18	0.35MAX	0.84MAX	φ 0.40	0.25MIN	40
1447170-7	FS1.78N63.5A40 JUMPER NOMEX	1.78	63.5	3.18	0.35MAX	0.84MAX	φ 0.40	0.25MIN	40
1447170-8	FS1.78N63.5A5 JUMPER NOMEX	1.78	63.5	3.18	0.35MAX	0.84MAX	φ 0.40	0.25MIN	5
1-1447170-4	FS1.78N76.2A30 JUMPER NOMEX	1.78	76.2	3.18	0.35MAX	0.84MAX	φ 0.40	0.25MIN	30

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL -

DWN -

CHK -

APVD -

PRODUCT SPEC 108-78002

APPLICATION SPEC -

WEIGHT 0

CUSTOMER DRAWING

SEE SHEET 1

TE Connectivity

FLEXSTRIP JUMPER

SIZE A3CAGE CODE 00779DRAWING NO C-1447169RESTRICTED TO -

SCALE NTS

SHEET 2 OF 9

REV A6

1470-19 (1/15)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

REVIS

P

LTR

DESCRIPTION

DATE

DWN

APVD

—

SEE SHEET 1

—

—

—

FS2.54N SERIES

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margin (G)	POS
9-1447170-8	FS2.54N15A18 JUMPER NOMEX	2.54	15.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	18
1447171-3	FS2.54N15A5 JUMPER NOMEX	2.54	15.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	5
1447171-5	FS2.54N15A8 JUMPER NOMEX	2.54	15.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	8
1447171-6	FS2.54N16A10 JUMPER NOMEX	2.54	16.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	10
2-1447171-0	FS2.54N17A8 JUMPER NOMEX	2.54	17.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	8
2-1447171-6	FS2.54N18A4 JUMPER NOMEX	2.54	18.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	4
3-1447171-5	FS2.54N20A20 JUMPER NOMEX	2.54	20.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	20
4-1447171-1	FS2.54N21A12 JUMPER NOMEX	2.54	21.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	12
4-1447171-9	FS2.54N30A10 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	10
5-1447171-8	FS2.54N30A15 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	15
6-1447171-2	FS2.54N30A17 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	17
6-1447171-3	FS2.54N30A18 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	18
6-1447171-6	FS2.54N30A20 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	20
8-1447171-3	FS2.54N30A4 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	4
8-1447171-5	FS2.54N30A7 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	7
8-1447171-8	FS2.54N30A9 JUMPER NOMEX	2.54	30.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	9
9-1447171-0	FS2.54N33A10 JUMPER NOMEX	2.54	33.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	10
9-1447171-3	FS2.54N35A13 JUMPER NOMEX	2.54	35.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	13
9-1447171-8	FS2.54N35A19 JUMPER NOMEX	2.54	35.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	19
2-1447172-0	FS2.54N40A22P39 JUMPER NOMEX	2.54	40.0	3.90	0.35MAX	0.84MAX	0.051	0.25MIN	22
2-1447172-9	FS2.54N40A28 JUMPER NOMEX	2.54	40.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	28
3-1447172-5	FS2.54N40A6 JUMPER NOMEX	2.54	40.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	6
3-1447172-7	FS2.54N40A8 JUMPER NOMEX	2.54	40.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	8
1473635-1	FS2.54N42A20 JUMPER NOMEX	2.54	42.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	20
1717056-4	FS2.54N55A15 JUMPER NOMEX	2.54	55.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	15
5-1447172-2	FS2.54N55A18 JUMPER NOMEX	2.54	55.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	18
5-1447172-6	FS2.54N55A30 JUMPER NOMEX	2.54	55.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	30
1717056-3	FS2.54N55A5 JUMPER NOMEX	2.54	55.0	3.18	0.35MAX	0.84MAX	0.051	0.25MIN	5
5-1447172-9	FS2.54N58A822 JUMPER NOMEX	2.54	58.0	3.18/4.5	0.35MAX	0.84MAX	0.051	0.25MIN	22
6-1447172-3	FS2.54N70A17PA JUMPER (PA4.0)	2.54	70.0	4.00	0.35MAX	0.84MAX	0.051	0.25MIN	17

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL -

DWN —

CHK —

APVD —

PRODUCT SPEC 108-78002

APPLICATION SPEC —

WEIGHT 0

SEE SHEET 1

TE Connectivity

FLEXSTRIP JUMPER

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-1447169

CUSTOMER DRAWING SCALE NTS SHEET 3 of 9 REV A6

1470-19 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

FS2N SERIES NO.1

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margin (G)	POS
7-1447173-2	FS2N101.6A12PA =JUMPER NOMEX	2.00	101.6	4.00	0.35MAX	0.84MAX	ø 0.40	0.25MIN	12
7-1447173-9	FS2N101.6A16PA =JUMPER NOMEX	2.00	101.6	4.00	0.35MAX	0.84MAX	ø 0.40	0.25MIN	16
8-1447173-2	FS2N101.6A20 =JUMPER NOMEX	2.00	101.6	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
8-1447173-9	FS2N101.6A3 =JUMPER NOMEX	2.00	101.6	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	3
9-1447173-4	FS2N101.6A6 =JUMPER NOMEX	2.00	101.6	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	6
1-1447174-5	FS2N12.7A10 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	10
2-1447174-0	FS2N12.7A13 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	13
2-1447174-1	FS2N12.7A14 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	14
2-1447174-5	FS2N12.7A17 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	17
2-1447174-9	FS2N12.7A20 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
3-1447174-0	FS2N12.7A22 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	22
3-1447174-1	FS2N12.7A24 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	24
3-1447174-3	FS2N12.7A26 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	26
3-1447174-8	FS2N12.7A4 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	4
4-1447174-0	FS2N12.7A5 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	5
4-1447174-2	FS2N12.7A6 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	6
1437127-7	FS2N12.7A8= JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	8
4-1447174-6	FS2N12.7A9 =JUMPER NOMEX	2.00	12.7	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	9
9-1447174-9	FS2N18A=JUMPER NOMEX	2.00	18.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	4
1447175-5	FS2N20A18 =JUMPER NOMEX	2.00	20.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	18
1447175-9	FS2N20A9 =JUMPER NOMEX	2.00	20.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	9
1-1447175-5	FS2N25.4A10 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	10
2-1447175-1	FS2N25.4A12 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	12
2-1447175-5	FS2N25.4A12PA=JUMPER (PA4.0)	2.00	25.4	4.00	0.35MAX	0.84MAX	ø 0.40	0.25MIN	12
2-1447175-6	FS2N25.4A13 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	13
3-1447175-2	FS2N25.4A14 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	14
3-1447175-7	FS2N25.4A16 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	16
4-1447175-0	FS2N25.4A17 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	17
4-1447175-3	FS2N25.4A19=JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	19
4-1447175-4	FS2N25.4A2 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	2
4-1447175-6	FS2N25.4A20 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
4-1447175-9	FS2N25.4A21 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	21
5-1447175-0	FS2N25.4A22 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	22
5-1447175-2	FS2N25.4A23 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	23
5-1447175-4	FS2N25.4A25 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	25
5-1447175-6	FS2N25.4A26 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	26
6-1447175-1	FS2N25.4A3 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	3
6-1447175-4	FS2N25.4A30 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	30
6-1447175-5	FS2N25.4A32 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	32
6-1447175-9	FS2N25.4A4 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	4
7-1447175-1	FS2N25.4A5 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	5
7-1447175-3	FS2N25.4A59 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	59
7-1447175-4	FS2N25.4A6 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	6
7-1447175-6	FS2N25.4A7 =JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	7
8-1447175-0	FS2N25.4A8=JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	8
8-1447175-4	FS2N25.4A9=JUMPER NOMEX	2.00	25.4	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	9
1437127-8	FS2N28A20= JUMPER NOMEX	2.00	28.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
1447176-6	FS2N30A25 =JUMPER NOMEX	2.00	30.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	25
1-1447176-2	FS2N32A15 =JUMPER NOMEX	2.00	32.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	15
2-1447176-1	FS2N35A7 =JUMPER NOMEX	2.00	35.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	7
1437127-9	FS2N36A20= JUMPER NOMEX	2.00	36.0	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
2-1447176-4	FS2N38.1A10 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	10
2-1447176-6	FS2N38.1A11 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	11
2-1447176-7	FS2N38.1A12= JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	12
3-1447176-1	FS2N38.1A13 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	13
3-1447176-6	FS2N38.1A14 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	14
4-1447176-0	FS2N38.1A15 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	15
4-1447176-7	FS2N38.1A16 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	16
5-1447176-2	FS2N38.1A17 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	17
5-1447176-3	FS2N38.1A18 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	18
5-1447176-5	FS2N38.1A19 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	19
5-1447176-7	FS2N38.1A2 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	2
5-1447176-8	FS2N38.1A20 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	20
5-1447176-9	FS2N38.1A21 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	21
6-1447176-1	FS2N38.1A22 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	22
6-1447176-3	FS2N38.1A23 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	23
6-1447176-4	FS2N38.1A24 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	24
6-1447176-6	FS2N38.1A25 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	25
6-1447176-8	FS2N38.1A26 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	26
7-1447176-5	FS2N38.1A29 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	29
7-1447176-6	FS2N38.1A3 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	3
7-1447176-9	FS2N38.1A31 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	31
8-1447176-4	FS2N38.1A4 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	4
8-1447176-7	FS2N38.1A5 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	5
9-1447176-2	FS2N38.1A6 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	6
9-1447176-4	FS2N38.1A7 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	7
9-1447176-5	FS2N38.1A8 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø 0.40	0.25MIN	8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL

FINISH

DWN —
CHK —
APVD —

SEE SHEET 1

PRODUCT SPEC
108-78002

APPLICATION SPEC
—

WEIGHT
0

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-1447169

SCALE SHEET REV

NTS 4 OF 9 A6

TE Connectivity

FLEXSTRIP JUMPER

—

1470-19 (1/15)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity FLEXSTRIP JUMPER — SIZECAGE CODEDRAWING NORESTRICTED TO A300779C-1447169—							
DIMENSIONS: mm MATERIAL—		CHK						NAME			
		APVD						DRAWING NO			
		PRODUCT SPEC						RESTRICTED TO			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SEE SHEET 1		108-78002		SCALE		SHEET		REV	
MATERIAL		FINISH		WEIGHT		CUSTOMER DRAWING		NTS		5 of 9	
				0						A6	

FS2N SERIES NO.2

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margh (G)	POS
1447177-1	FS2N38.1A9 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	9
1447177-7	FS2N38.1B12 =JUMPER NOMEX	2.00	38.1	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	12
1-1447177-4	FS2N40A14 =JUMPER NOMEX	2.00	40.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	14
2-1447177-2	FS2N42A11 =JUMPER NOMEX	2.00	42.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	11
2-1447177-3	FS2N42A15 =JUMPER NOMEX	2.00	42.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	15
2-1447177-5	FS2N42A9 =JUMPER NOMEX	2.00	42.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	9
3-1447177-2	FS2N50.8A10 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	10
3-1447177-5	FS2N50.8A11 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	11
3-1447177-8	FS2N50.8A12 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	12
4-1447177-1	FS2N50.8A13 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	13
4-1447177-2	FS2N50.8A14 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	14
4-1447177-4	FS2N50.8A15 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	15
5-1447177-2	FS2N50.8A16 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	16
5-1447177-5	FS2N50.8A17 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	17
5-1447177-6	FS2N50.8A18 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	18
5-1447177-8	FS2N50.8A19 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	19
6-1447177-0	FS2N50.8A2 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	2
6-1447177-3	FS2N50.8A20PA =JUMPER NOMEX	2.00	50.8	4.00	0.35MAX	0.84MAX	ø0.40	0.25MIN	20
6-1447177-4	FS2N50.8A21 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	21
6-1447177-6	FS2N50.8A22 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	22
6-1447177-8	FS2N50.8A23 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	23
6-1447177-9	FS2N50.8A24 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	24
7-1447177-1	FS2N50.8A25 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	25
7-1447177-2	FS2N50.8A26 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	26
7-1447177-5	FS2N50.8A3 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	3
7-1447177-6	FS2N50.8A30 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	30
7-1447177-9	FS2N50.8A33 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	33
8-1447177-4	FS2N50.8A4 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	4
8-1447177-5	FS2N50.8A40 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	40
8-1447177-9	FS2N50.8A6 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	6
9-1447177-1	FS2N50.8A7 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	7
9-1447177-4	FS2N50.8A8 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	8
9-1447177-6	FS2N50.8A9 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	9
9-1447178-8	FS2N50.8AB6 =JUMPER NOMEX	2.00	50.8	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	6
1447178-8	FS2N63.5A12 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	12
1447178-9	FS2N63.5A13 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	13
1-1447178-1	FS2N63.5A15 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	15
1-1447178-5	FS2N63.5A18PA =JUMPER (PA4.0)	2.00	63.5	4.00	0.35MAX	0.84MAX	ø0.40	0.25MIN	16
2-1447178-1	FS2N63.5A20 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	20
2-1447178-3	FS2N63.5A21 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	21
2-1447178-5	FS2N63.5A25 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	25
2-1447178-8	FS2N63.5A28 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	28
2-1447178-9	FS2N63.5A3 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	3
3-1447178-0	FS2N63.5A30 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	30
3-1447178-8	FS2N63.5A4 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	4
3-1447178-9	FS2N63.5A5 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	5
4-1447178-1	FS2N63.5A6 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	6
4-1447178-3	FS2N63.5A8 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	8
4-1447178-4	FS2N63.5A9 =JUMPER NOMEX	2.00	63.5	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	9
5-1447178-0	FS2N72A28 =JUMPER NOMEX	2.00	72.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	25
5-1447178-1	FS2N72A28 =JUMPER NOMEX	2.00	72.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	28
5-1447178-2	FS2N72A32 =JUMPER NOMEX	2.00	72.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	32
5-1447178-9	FS2N76.2A12 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	12
6-1447178-2	FS2N76.2A14 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	14
7-1447178-1	FS2N76.2A20 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	20
7-1447178-2	FS2N76.2A20PA =JUMPER NOMEX	2.00	76.2	4.00	0.35MAX	0.84MAX	ø0.40	0.25MIN	20
7-1447178-4	FS2N76.2A26 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	26
7-1447178-5	FS2N76.2A28 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	28
8-1447178-1	FS2N76.2A4 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	4
1376986-1	FS2N76.2A40 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	40
8-1447178-4	FS2N76.2A5 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	5
8-1447178-6	FS2N76.2A6 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	6
8-1447178-7	FS2N76.2A7 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	7
8-1447178-8	FS2N76.2A8 =JUMPER NOMEX	2.00	76.2	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	8
9-1447178-5	FS2N80A28 =JUMPER NOMEX	2.00	80.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	28
9-1447178-6	FS2N80A32 =JUMPER NOMEX	2.00	80.0	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	32
1447179-2	FS2N88.9A10 =JUMPER NOMEX	2.00	88.9	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	10
1447179-4	FS2N88.9A12 =JUMPER NOMEX	2.00	88.9	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	12
1-1447179-6	FS2N88.9A20PA =JUMPER (PA4.0)	2.00	88.9	4.00	0.35MAX	0.84MAX	ø0.40	0.25MIN	20
2-1447179-6	FS2N88.9A6 =JUMPER NOMEX	2.00	88.9	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	6
2-1447179-8	FS2N88.9A8 =JUMPER NOMEX	2.00	88.9	3.18	0.35MAX	0.84MAX	ø0.40	0.25MIN	8

FSN SERIES NO.2


THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margin (G)	POS
7-1447183-3	FSN-2.5A-10= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	10
7-1447183-5	FSN-2.5A-11= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	11
7-1447183-7	FSN-2.5A-12= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	12
7-1447183-8	FSN-2.5A-13= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	13
8-1447183-0	FSN-2.5A-14= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	14
4-1437134-9	FSN-2.5A-15= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	15
8-1447183-2	FSN-2.5A-16= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	16
8-1447183-4	FSN-2.5A-18= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	18
8-1447183-5	FSN-2.5A-2= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	2
8-1447183-6	FSN-2.5A-20= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	20
5-1437134-7	FSN-2.5A-22= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	22
6-1437134-2	FSN-2.5A-3= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	3
6-1437134-3	FSN-2.5A-30= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	30
9-1447183-6	FSN-2.5A-4= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	4
9-1447183-8	FSN-2.5A-5= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	5
1447184-1	FSN-2.5A-6= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	6
1447184-3	FSN-2.5A-7= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	7
1447184-7	FSN-2.5A-9= JUMPER NOMEX	2.54	12.7	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	9
3-1437137-4	FSN-21.5A-10= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	10
3-1437137-6	FSN-21.5A-11= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	11
4-1437137-1	FSN-21.5A-13= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	13
4-1437137-2	FSN-21.5A-14= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	14
4-1437137-3	FSN-21.5A-16= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	15
4-1437137-6	FSN-21.5A-17= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	17
4-1447184-0	FSN-21.5A-18= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	18
4-1437137-8	FSN-21.5A-19= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	19
4-1437137-9	FSN-21.5A-2= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	2
4-1447184-2	FSN-21.5A-20= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	20
5-1437137-4	FSN-21.5A-22= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	22
5-1437137-5	FSN-21.5A-23= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	23
5-1437137-7	FSN-21.5A-24= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	24
5-1437137-8	FSN-21.5A-25= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	25
5-1437137-9	FSN-21.5A-26= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	26
5-1447184-0	FSN-21.5A-27= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	27
5-1447184-6	FSN-21.5A-3= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	3
6-1437137-3	FSN-21.5A-30= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	30
6-1437137-4	FSN-21.5A-32= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	32
6-1447184-2	FSN-21.5A-33= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	33
6-1437137-7	FSN-21.5A-4= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	4
6-1447184-8	FSN-21.5A-5= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	5
7-1437137-2	FSN-21.5A-6= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	6
7-1447184-3	FSN-21.5A-7= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	7
7-1447184-8	FSN-21.5A-8= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	8
7-1437137-8	FSN-21.5A-9= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	9
9-1437137-4	FSN-21.5B-6= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	6
8-1447184-6	FSN-21.5B-9= JUMPER NOMEX	2.54	38.1	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	9
6-1437139-7	FSN-21A-10= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	10
6-1437139-9	FSN-21A-11= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	11
7-1437139-1	FSN-21A-12= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	12
7-1437139-3	FSN-21A-13= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	13
7-1437139-4	FSN-21A-14= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	14
7-1437139-7	FSN-21A-15= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	15
7-1437139-9	FSN-21A-16= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	16
8-1437139-0	FSN-21A-17= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	17
8-1437139-1	FSN-21A-18= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	18
8-1437139-2	FSN-21A-19= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	19
8-1437139-3	FSN-21A-2= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	2
8-1437139-4	FSN-21A-20= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	20
8-1437139-5	FSN-21A-21= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	21
8-1437139-6	FSN-21A-22= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	22
8-1437139-9	FSN-21A-25= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	25
9-1437139-0	FSN-21A-26= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	26
9-1437139-1	FSN-21A-27= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	27
9-1437139-2	FSN-21A-28= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	28
9-1437139-7	FSN-21A-3= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	3
9-1437139-8	FSN-21A-30= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	30
1437140-9	FSN-21A-4= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	4
1-1437140-1	FSN-21A-5= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	5
1-1437140-4	FSN-21A-6= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	6
1-1437140-6	FSN-21A-7= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	7
2-1437140-1	FSN-21A-9= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	9
5-1447185-6	FSN-21A-9PA = JUMPER (PA4.0)	2.54	25.4	4.00	0.35MAX	0.84MAX	ø 0.51	0.25MIN	9
5-1447185-9	FSN-21AB-1= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	14
6-1447185-2	FSN-21AB-5= JUMPER NOMEX	2.54	25.4	3.18	0.35MAX	0.84MAX	ø 0.51	0.25MIN	5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

MATERIAL -

DWN -
CHK -
APVD -

SEE SHEET 1

PRODUCT SPEC
108-78002

APPLICATION SPEC
-

WEIGHT
0

CUSTOMER DRAWING

NAME
FLEXSTRIP JUMPER

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1447169

RESTRICTED TO
-

SCALE
NTS

SHEET
7 of 9

REV
A6

TE Connectivity

108-78002

1447185-2

A

B

C

D

A

B

C

D

FSN SERIES NO.3

P/N	Description	Pitch (A)	Tape Length (B)	Pin Length (C)	Tape Thickness (D)	Tape Thickness (E)	Pin Diameter (F)	Margin (G)	POS
2-1437141-9	FSN-22.5A-10= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	10
3-1437141-0	FSN-22.5A-11= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	11
3-1437141-1	FSN-22.5A-12= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	12
7-1447185-4	FSN-22.5A-14PA JUMPER NOMEX	2.54	63.5	4.00	0.35MAX	0.84MAX	ø0.51	0.25MIN	14
3-1437141-4	FSN-22.5A-15= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	15
3-1437141-5	FSN-22.5A-16= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	16
3-1437141-7	FSN-22.5A-18=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	18
8-1447185-8	FSN-22.5A-19=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	19
3-1437141-9	FSN-22.5A-20= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	20
4-1437141-2	FSN-22.5A-22= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	22
9-1447185-6	FSN-22.5A-25=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	25
1447186-1	FSN-22.5A-26=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	26
4-1437141-9	FSN-22.5A-3= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	3
1447186-6	FSN-22.5A-30=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	30
1447186-8	FSN-22.5A-31=JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	31
5-1437141-1	FSN-22.5A-4= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	4
5-1437141-2	FSN-22.5A-5= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	5
5-1437141-3	FSN-22.5A-8= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	6
5-1437141-4	FSN-22.5A-7= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	7
5-1437141-5	FSN-22.5A-9= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	8
5-1437141-6	FSN-22.5A-9= JUMPER NOMEX	2.54	63.5	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	9
2-1437142-8	FSN-22A-10= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	10
3-1437142-0	FSN-22A-11= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	11
3-1437142-2	FSN-22A-12= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	12
3-1437142-3	FSN-22A-13= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	13
3-1437142-4	FSN-22A-14= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	14
3-1437142-5	FSN-22A-15= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	15
3-1437142-6	FSN-22A-16= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	16
3-1437142-7	FSN-22A-17= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	17
3-1437142-8	FSN-22A-18= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	18
3-1437142-9	FSN-22A-19= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	19
4-1437142-0	FSN-22A-2= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	2
4-1437142-1	FSN-22A-20= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	20
4-1437142-3	FSN-22A-21= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	21
4-1437142-4	FSN-22A-22= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	22
4-1437142-5	FSN-22A-23= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	23
4-1437142-6	FSN-22A-24= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	24
4-1437142-9	FSN-22A-25= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	25
5-1437142-0	FSN-22A-26= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	26
7-1447186-7	FSN-22A-28=JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	28
5-1437142-2	FSN-22A-3= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	3
5-1437142-3	FSN-22A-30= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	30
8-1447186-5	FSN-22A-31=JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	31
9-1447186-0	FSN-22A-34=JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	34
9-1447186-1	FSN-22A-37=JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	37
5-1437142-9	FSN-22A-4= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	4
9-1447186-7	FSN-22A-4PA =JUMPER (PA4.0)	2.54	50.8	4.00	0.35MAX	0.84MAX	ø0.51	0.25MIN	4
6-1437142-2	FSN-22A-5= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	5
1447187-1	FSN-22A-5PA =JUMPER (PA4.0)	2.54	50.8	4.00	0.35MAX	0.84MAX	ø0.51	0.25MIN	5
6-1437142-7	FSN-22A-6= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	6
6-1437142-9	FSN-22A-7= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	7
7-1437142-2	FSN-22A-8= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	8
1447178-7	FSN-22A-8PA= JUMPER NOMEX	2.54	50.8	4.00	0.35MAX	0.84MAX	ø0.51	0.25MIN	8
7-1437142-5	FSN-22A-9= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	9
1-1447187-3	FSN-22AB-9=JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	8
1437143-2	FSN-22B-20= JUMPER NOMEX	2.54	50.8	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	20
6-1437143-4	FSN-23.5A-10= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	10
6-1437143-5	FSN-23.5A-11= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	11
6-1437143-6	FSN-23.5A-12= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	12
6-1437143-8	FSN-23.5A-14= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	14
2069384-1	FSN-23.5A-21= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	ø0.51	0.25MIN	21

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

B/C ANGLES ± -

MATERIAL

-

FINISH

-

DWN -

CHK -

APVD -

SEE SHEET 1

PRODUCT SPEC

108-78002

APPLICATION SPEC

-

WEIGHT

0

CUSTOMER DRAWING

NAME

FLEXSTRIP JUMPER

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1447169

-

SCALE

NTS

SHEET

8 of 9

REV

A6

TE Connectivity

FLEXSTRIP JUMPER

-

1470-19 (1/15)

A

B

C

D

1

2

3

4

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

FSN SERIES NO.4

P/N	Description	Pitch (A)	Tap Length (B)	Pin Length (C)	Tap Thickness (D)	Tap Thickness (E)	Pin Diameter (F)	Margin (G)	POS
8-1437143-5	FSN-23A-8-8= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	8
8-1437143-6	FSN-23A-9-9= JUMPER NOMEX	2.54	88.9	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	9
2-1437144-5	FSN-23A-10= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	10
2-1437144-7	FSN-23A-11= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	11
3-1437144-0	FSN-23A-13= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	13
3-1437144-1	FSN-23A-14= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	14
3-1437144-3	FSN-23A-15= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	15
3-1437144-4	FSN-23A-16= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	16
3-1437144-6	FSN-23A-18= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	18
4-1447187-2	FSN-23A-18-3.5= JUMPER (PL3.5)	2.54	76.2	3.50	0.35MAX	0.84MAX	φ0.51	0.25MIN	18
3-1437144-8	FSN-23A-19= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	19
4-1437144-0	FSN-23A-20= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	20
4-1437144-2	FSN-23A-21= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	21
4-1437144-3	FSN-23A-22= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	22
4-1437144-4	FSN-23A-23= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	23
4-1437144-5	FSN-23A-24= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	24
4-1437144-6	FSN-23A-25= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	25
4-1437144-7	FSN-23A-26= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	26
5-1437144-1	FSN-23A-30= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	30
5-1437144-6	FSN-23A-4= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	4
5-1437144-8	FSN-23A-5= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	5
5-1437144-9	FSN-23A-6= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	6
6-1447187-9	FSN-23A-6PA= JUMPER (PA4.0)	2.54	76.2	4.00	0.35MAX	0.84MAX	φ0.51	0.25MIN	6
6-1437144-0	FSN-23A-7= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	7
7-1447187-1	FSN-23A-8-3.5= JUMPER (PL3.5)	2.54	76.2	3.18 ^{+0.76}	0.35MAX	0.84MAX	φ0.51	0.25MIN	8
6-1437144-3	FSN-23A-9= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	9
7-1447187-8	FSN-23B-12= JUMPER NOMEX	2.54	76.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	12
4-1437145-8	FSN-24A-10= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	10
8-1447178-7	FSN-24A-12PA= JUMPER NOMEX	2.54	101.6	4.00	0.35MAX	0.84MAX	φ0.51	0.25MIN	12
5-1437145-4	FSN-24A-14= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	14
5-1437145-6	FSN-24A-15= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	15
6-1437145-4	FSN-24A-2= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	2
6-1437145-5	FSN-24A-20= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	20
7-1437145-1	FSN-24A-25= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	25
8-1437145-1	FSN-24A-4= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	4
8-1437145-4	FSN-24A-5= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	5
8-1437145-6	FSN-24A-7= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	7
8-1437145-8	FSN-24A-8= JUMPER NOMEX	2.54	101.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	8
2-1447188-2	FSN-25A-10= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	10
2-1447188-4	FSN-25A-11= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	11
2-1447188-8	FSN-25A-15= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	15
3-1447188-3	FSN-25A-20= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	20
3-1447188-6	FSN-25A-22= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	22
4-1447188-0	FSN-25A-3= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	3
4-1447188-7	FSN-25A-6= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	6
4-1447188-9	FSN-25A-7= JUMPER NOMEX	2.54	127.0	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	7
9-1437146-1	FSN-26A-12= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	12
9-1437146-3	FSN-26A-1= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	14
9-1437146-6	FSN-26A-16= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	16
6-1447188-3	FSN-26A-2= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	2
1437147-9	FSN-26A-4= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	4
1-1437147-1	FSN-26A-5= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	5
1-1437147-3	FSN-26A-7= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	7
6-1447188-8	FSN-26A-8= JUMPER NOMEX	2.54	152.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	8
8-1437147-9	FSN-28A-3= JUMPER NOMEX	2.54	203.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	3
9-1437147-1	FSN-28A-4= JUMPER NOMEX	2.54	203.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	4
9-1437147-2	FSN-28A-5= JUMPER NOMEX	2.54	203.2	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	5
9-1447188-0	FSN-29A-4= JUMPER NOMEX	2.54	228.6	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	4
4-1437148-7	FSN-31A-3= JUMPER NOMEX	3.18	25.4	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	3
8-1437149-9	FSN-52A-17= JUMPER NOMEX	5.08	50.8	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	17
9-1437149-9	FSN-52A-2= JUMPER NOMEX	5.08	50.8	3.18	0.35MAX	0.84MAX	φ0.51	0.25MIN	2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL

—

FINISH

—

DWN —
CHK —
APVD —

SEE SHEET 1

PRODUCT SPEC
108-78002

APPLICATION SPEC
—

WEIGHT
0

CUSTOMER DRAWING

SCALE NTS

SHEET 9 OF 9

REV A6

TE Connectivity

FLEXSTRIP JUMPER

—

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1447169

—

1470-19 (1/15)